


Surname: First name:			
Adress:			
Checklist for the installation of a VISION AQU cabinet.	UA® water filter system onto you	r rinking water connection, in I	the kitchen in the sink base
Dimensions/space requirement in the sink base cabinet (please note the distance between the odour trap and the wall)	Verdanium MAX H= 635 mm W= 205 mm D= 460 mm	Verdanium Home H= 397 mm W= 248 mm D= 374 mm	VA-Mini H= 275 mm W= 224 mm D= 247 mm
Water quantity (liters/minute)	Minimum water flow Verdanium MAX – 4 l/min.		
Power connection (with grounding) available?	Yes Mandatory		
1. Withdrawal tap			
Required height for the one-way tap (height wi	ith base 212 mm)		
1.2. Drilled hole for one-way tap possible?1.3. Mounting of the one-way tap possible? (Diameter for the screw connection from below is Ø 42 mm).3-way tap optionally possible?	Yes Yes Yes	No No No	
Diameter for the screw connection of an optional 3-way tap is ø 35 mm		<u> </u>	
2. Water connection			
Water connection within max. 3 m distance of the water filter system?	Yes	No	
Washing machine/dishwasher available?	Yes	No	
In the absence of washing machine/dishwasher: Is a 3/4" cold water connection available?	Yes If a 3/4" connection is available, pstandard installation kit for the wsystem.	vater filter connection ada	ection is available, a separate pter must be fitted to the on in addition to the standard
3. Waster water			
3.1. Is there a drain available? (no odour trap made of lex pipe)	Yes	No	
With an odour trap made of a flex pipe, a dra	in modification is necessary!		
3.2. Max. diameter in front of the odour trap (tube) ø 40 mm? Distance to the water filter system: max. 3 m?	Yes Yes	No No	
If there is no connection option for waste wate	er, it can also be discharged into the	e sink via a separate withdrawal	tap adapter.
4. Connection of kitchen appliances			
Do you want to supply kitchen appliances with ultra-pure water?	Yes	No	
If you would like to supply your kitchen appliances with ultra-pure water, dishwashers and/or washing machines can be connected via an additional adapter and storage tank as a buffer.			
Connection of washing machine/dishwasher is possible with water filter systems Verdanium MAX and Verdanium Home.			
Dimensions to be observed/space requirements for storage tanks	3 l – H= 250 mm without stop co Ø= 165 mm	ck 10 l – H= 370 m Ø= 285 m	m without stop cock nm





You can find a video installation tutorial online using the following QR code: https://www.vision-aqua.de/agentenbereich/videos/





